



EUCLID CHEMICAL

DURAL FAST SET LV

**RAPID-SETTING, LOW VISCOSITY, HIGH MODULUS
EPOXY ADHESIVE**

PACKAGING

4 gal (15 L) unit
Code: TD5324104
10 gal (38 L) unit
Code: TD5324110
22 oz (650 mL) dual cartridge
(case of 12)
Code: TD5324122
10 oz (300 mL) single cartridge
(case of 24)
Code: TD5324115

CLEAN UP

Clean tools and application equipment immediately with acetone, xylene, or MEK. Clean spills or drips with the same solvents while still wet. Hardened DURAL FAST SET LV will require mechanical abrasion for removal.

SHELF LIFE

2 years in original, unopened package

SPECIFICATIONS AND COMPLIANCES

- Complies with ASTM C881 Types I and IV, Grade 1, Classes B and C
- Meets the requirements of AASHTO M 235
- Canadian MTQ

DESCRIPTION

DURAL FAST SET LV is a two-component, 100% solids, moisture insensitive, rapid-setting epoxy adhesive and binder for numerous applications. This high modulus, low viscosity epoxy resin is the perfect solution for general bonding applications and for injecting cracks in concrete and a variety of other substrates. DURAL FAST SET LV can be used in temperatures as low as 40 °F (4 °C) and rising.

PRODUCT CHARACTERISTICS

FEATURES/BENEFITS

- Exceptional adhesion to construction materials
- Low viscosity penetrates deep into cracks
- Easy to use 1:1 mix ratio
- Moisture insensitive
- Tenacious bond strength

PRIMARY APPLICATIONS

- Bonding of concrete, masonry or wood
- Injection resin for cracked, structural substrates
- Gravity feed cracks in concrete slabs
- Mix with dried silica sand to create a repair mortar

APPEARANCE

Part A liquid is pale yellow in color and Part B liquid is amber in color.

COVERAGE

For injection, 1 neat gal (3.8 L) yields 231 in³ (3,785 cm³) of epoxy. 1 gal (3.8 L) of neat DURAL FAST SET LV epoxy mixed with 3 gal (11.4 L) of dry 20/40 mesh silica sand will yield approximately 643 in³ (10,537 cm³) of mortar.

Note: Coverage rates are approximate. Actual coverage depends on temperature, texture, and substrate porosity.

TECHNICAL INFORMATION

The following are typical values obtained under laboratory conditions. Expect reasonable variation under field conditions.

Test Method	Test Property	Result
ASTM D2556	Mixed Viscosity	800 cp
ASTM C881	Gel Time	6 minutes
ASTM C882	Bond Strength	2 days: 2,300 psi (15.9 MPa) 14 days: 2,600 psi (17.9 MPa)
ASTM D570	Water Absorption	24 hours: 0.1%
ASTM D648	Heat Deflection Temperature	135 °F (57 °C)
ASTM D2566	Linear Coefficient of Shrinkage	0.001
ASTM D695	Compressive Yield	1 hour: 4,000 psi (27.6 MPa) 2 hour: 10,500 psi (72.4 MPa) 4 hour: 13,000 psi (89.6 MPa) 7 days: 15,500 psi (106.9 MPa)
ASTM D695	Compressive Modulus	7 days: 575,000 psi (3,964 MPa)
ASTM D638	Tensile Strength	7 days: 10,000 psi (68.9 MPa)
ASTM D638	Elongation at Break	1.9%

WARRANTY: The Euclid Chemical Company ("Euclid") solely and expressly warrants that its products shall be free from defects in materials and workmanship for one (1) year from the date of purchase. Unless authorized in writing by an officer of Euclid, no other representations or statements made by Euclid or its representatives, in writing or orally, shall alter this warranty. EUCLID MAKES NO WARRANTIES, IMPLIED OR OTHERWISE, AS TO THE MERCHANTABILITY OR FITNESS FOR ORDINARY OR PARTICULAR PURPOSES OF ITS PRODUCTS AND EXCLUDES THE SAME. If any Euclid product fails to conform with this warranty, Euclid will replace the product at no cost to Buyer. Replacement of any product shall be the sole and exclusive remedy available and buyer shall have no claim for incidental or consequential damages. Any warranty claim must be made within one (1) year from the date of the claimed breach. Euclid does not authorize anyone on its behalf to make any written or oral statements which in any way alter Euclid's installation information or instructions in its product literature or on its packaging labels. Any installation of Euclid products which fails to conform with such installation information or instructions shall void this warranty. Product demonstrations, if any, are done for illustrative purposes only and do not constitute a warranty or warranty alteration of any kind. Buyer shall be solely responsible for determining the suitability of Euclid's products for the Buyer's intended purposes.

DIRECTIONS FOR USE

Surface Preparation: The surface must be structurally sound, dry, clean and free of grease, oil, curing compounds, soil, dust and other contaminants. Surface laitance must be removed. Concrete surfaces must be roughened and made absorptive, preferably by mechanical means, and then thoroughly cleaned of all dust and debris. If the surface was prepared by chemical means (acid etching), a water/baking soda or water/ammonia mixture, followed by a clean water rinse, must be used for cleaning, in order to neutralize the substrate. Allow substrate to dry before application. Route cracks and blow dust/debris from them with oil-free compressed air. Following surface preparation, the strength of the surface can be tested if quantitative results are required by project specifications. An elcometer or similar tensile pull tester may be used in accordance with ASTM D4541, and the tensile pull-off strength should be at least 250 psi (1.7 MPa). When DURAL FAST SET LV is being mixed to a mortar consistency and then used to perform patching and repairs, provide a CSP of 3 to 5 in accordance with ICRI 310.2. When coating steel, all contamination should be removed and the steel surface prepared to a "near white" finish (SSPC SP10) using clean, dry blasting media.

Mixing: Mix bulk units of DURAL FAST SET LV using a low-speed drill and a mixing paddle. Pre-mix Part A and Part B separately for approximately 1 minute each. Combine Part A and Part B in a 1:1 ratio by volume, then mix thoroughly for 3 minutes.

To make DURAL FAST SET LV mortar, gradually add clean, dry, 20/40 mesh silica sand to previously mixed DURAL FAST SET LV epoxy and mix thoroughly for 1 to 2 minutes. The mix ratio of aggregate to mixed epoxy is approximately 3:1 by volume, but can be modified depending on the desired consistency of the mortar.

Scrape the bottom and sides of the containers at least once during mixing. Do not scrape bottom or sides of the container once mixing operations have ceased; doing so may result in unmixed resin or hardener being applied to the substrate. Unmixed resin or hardener will not cure properly. Do not aerate the material during mixing. To keep aeration to a minimum, the recommended mixing paddles are #P1 or #P2 as found in ICRI Guideline 320.5R-2014.

Application: Pressure injecting vertical cracks: Attach injection ports and seal the face of the crack with DURAL 452 GEL or DURAL FAST SET GEL. Allow the sealing gel to sufficiently harden before injecting, to prevent blowouts. Pump DURAL FAST SET LV into the crack via the injection ports, using two-component pressure injection equipment. Start at the bottom of the crack and work upwards from port to port. Cap off ports as you proceed up the crack to ensure that DURAL FAST SET LV is kept contained within the crack. DO NOT INJECT IF WATER IS LEAKING FROM THE CRACK. **Horizontal cracks:** Open cracks by mechanical means and ensure that the prepared crack is free of all debris and standing water. If pressure injecting, instructions are the same as for vertical cracks. If gravity feeding, pump DURAL FAST SET LV until cracks are completely filled. If working on an elevated slab, ensure the bottom of the slab is sealed prior to injecting or gravity feeding the crack, to ensure epoxy does not leak through. **Anchoring bolts, dowels, pins:** DURAL FAST SET LV can be used neat or as a mortar to grout vertically-aligned anchors (into a horizontal substrate). The anchor hole should be free of all debris before grouting. The optimum hole size is 1/16" (1.6 mm) annular space (1/8" (3.2 mm) larger diameter than anchor diameter). Depth of embedment is typically 10 to 15 times anchor diameter. **Patching and repairs:** Apply DURAL FAST SET LV neat as a primer coat to the prepared concrete surface. Mix the DURAL FAST SET LV into an epoxy mortar and apply to the area by trowel or spatula in lifts of 1" to 1-1/2" (25 to 38 mm) before the neat primer coat becomes tack free. Allow each lift to reach initial set before applying subsequent lifts.

PRECAUTIONS/LIMITATIONS

- Store DURAL FAST SET LV indoors, protected from moisture, at temperatures between 50 °F and 90 °F (10 °C and 32 °C)
- Surface and ambient temperature during applications should be between 40 °F and 90 °F (4 °C and 32 °C)
- Material temperatures should be at least 40 °F (4 °C) and rising
- Working time and cure time will decrease as the temperature increases, and will increase as the temperature decreases
- Do not thin DURAL FAST SET LV
- DURAL FAST SET LV will discolor upon prolonged exposure to ultraviolet light and high-intensity artificial lighting.
- DURAL FAST SET LV is not to be used as a finished/aesthetic coating
- Do not use DURAL FAST SET LV for horizontally-aligned anchors (into a vertical substrate)
- Do not use DURAL FAST SET LV for overhead anchoring
- Maximum application thickness of DURAL FAST SET LV mortar is 1.5" per lift.
- In all cases, consult the product Safety Data Sheet before use

Rev. 05.25

WARRANTY: The Euclid Chemical Company ("Euclid") solely and expressly warrants that its products shall be free from defects in materials and workmanship for one (1) year from the date of purchase. Unless authorized in writing by an officer of Euclid, no other representations or statements made by Euclid or its representatives, in writing or orally, shall alter this warranty. EUCLID MAKES NO WARRANTIES, IMPLIED OR OTHERWISE, AS TO THE MERCHANTABILITY OR FITNESS FOR ORDINARY OR PARTICULAR PURPOSES OF ITS PRODUCTS AND EXCLUDES THE SAME. If any Euclid product fails to conform with this warranty, Euclid will replace the product at no cost to Buyer. Replacement of any product shall be the sole and exclusive remedy available and buyer shall have no claim for incidental or consequential damages. Any warranty claim must be made within one (1) year from the date of the claimed breach. Euclid does not authorize anyone on its behalf to make any written or oral statements which in any way alter Euclid's installation information or instructions in its product literature or on its packaging labels. Any installation of Euclid products which fails to conform with such installation information or instructions shall void this warranty. Product demonstrations, if any, are done for illustrative purposes only and do not constitute a warranty or warranty alteration of any kind. Buyer shall be solely responsible for determining the suitability of Euclid's products for the Buyer's intended purposes.